

Static Decay Timer

PDT-740B

Data Sheet

Measure decay times for ionizers and materials

The PDT-740B Static Decay Timer is designed to measure the time required for a 1,000 Volt charge to dissipate to less than 100, 50 or less than 10 Volts in tenths of a second. This extremely useful accessory is used with the Prostat PFM-711A Field Meter and CPM-720A Charge Plate Monitor to evaluate Ionizer Decay Time in accordance with ESD Association Ionization Standard ANSI/ESD STM3.1.

The PDT-740B may be used to evaluate the static decay capabilities of materials, personnel, equipment and other products. It is compatible with most portable CPM's and field meters having an analog output (10,000 Volts equals 1 Volt). Completely automatic, the PDT-740B is simple to operate and easy to use.



Distributed by

Pro-Pack Materials Pte Ltd

The ESD & Cleanroom Specialist

• No. 2, Bukit Batok Street 23, #08-05 Bukit Batok Connection, Singapore 659554.

✉ sales@pro-pack.com.sg

☎ (65) 6354 1511

Data Sheet

Specifications for the PDT-740B Static Decay Timer

Controls	OFF-ON Cut Off Voltage, 10, 50 and 100 Volts (Selects Voltage to stop timing)
Indicators	Green LED: Decay Cycle Ready > $\pm 1\text{kV}$, CPM voltage > $\pm 1,000$ Volts Red LED: Timing in Progress, CPM voltage decay timing activated LOBAT: Displayed when battery voltage < 6.0 Volts
Display	Liquid Crystal Display (LCD) displays elapsed decay time from $\pm 1,000$ Volts to selected Cut Off voltage in seconds and tenths of a second (00.0)
Polarity	Automatically senses Positive & Negative voltage references
Zero & Reset	Automatically Resets Timer and Display to 00.0 when Charge Plate Monitor voltage > $\pm 1\text{kV}$. Reset indicated when Green LED Decay Cycle Ready LED is ON
Response	Approximately 200 milliseconds in combination with PFM-711A and Charge Plate Monitor
Timing Range	From 0.2 to 159.9 seconds
Timing Setpoints	Reset when voltage input $100\text{mv} \pm 2\text{ mv}$ (1,000 Field Meter Volts $\pm 20\text{ V}$) Cut Off Voltage @ 100 V: $10\text{mv} \pm 0.2\text{ mv}$ (100 Field Meter Volts $\pm 2\text{ V}$) Cut Off Voltage @ 50 V: $5\text{mv} \pm 0.2\text{ mv}$ (50 Field Meter Volts $\pm 2\text{ V}$) Cut Off Voltage @ 10 V: $1\text{mv} \pm 0.2\text{ mv}$ (10 Field Meter Volts $\pm 2\text{ V}$)
Accuracy	Typically < $\pm 5\%$
Power	One (1) standard 9 Volts battery, PROCELL, Eveready #216 (NEDA 1604, JIS 006P, IEC 6F22) Eveready #216
Battery Life	> 40 hours typical
Dimension (LxWxH)	4.50" x 2.75" x 1.0" (11.4 cm x 7 cm x 2.5 cm)
Weight	6.5 oz with battery installed (184g)

1072 Tower Lane, Bensenville, IL 60106 USA
Phone +1 (630) 238-8883 Fax +1 (630) 238-9717

www.prostatcorp.com

©2017 Prostat Corporation. All rights reserved. Prostat, Prostat Corporation, Qube and the Prostat logo are trademarks or registered trademarks of Prostat Corporation or one of its affiliated companies in the United States and/or other countries. All other trademarks or registered trademarks are the property of their respective owners. Complying with all applicable copyright laws is the responsibility of the user. Prostat reserves the right to change, without notice, product offerings or specifications. Printed in U.S.A. REV2: 06/20/07



Distributed by

Pro-Pack Materials Pte Ltd
The ESD & Cleanroom Specialist

📍 No. 2, Bukit Batok Street 23, #08-05 Bukit Batok Connection, Singapore 659554. ✉ sales@pro-pack.com.sg ☎ (65) 6354 1511